

■バックアップ時間の目安（生産終了機種）■

※周間温度20℃・バッテリー初期状態の場合、本バックアップ時間はあくまでも参考値となります。バッテリーの寿命および外部環境（温度など）によって変わります。

●常時インバータ給電方式

時間単位：(分)

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	600W	700W	800W	900W	1000W	1100W	1200W	1300W	1400W	1500W	1600W	1700W	1800W	1900W	2000W	2100W	2200W	2300W	2400W	2500W	2600W	2700W	2800W	2900W	3000W	3100W	3200W	3300W	3400W	3500W
BU5002RWL	660	480	320	200	140	106	83	68	57	50	44	39	34	31	27.7	25	23	21	19	18	17	16	15	14	13	12	11.3	10.6	10	9.3	8.6	8	7.6	7.3	7	6	5
BU3002RWL	450	260	165	93	63	45	34.0	28	22	19	16	15	13	11	10	9	8.2	7.5	6.7	6	5.6	5.2	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BU2002RWL	360	190	110	60	39	27	20	16	13	12	10.6	9.5	8	7	6	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BU1002RW	140	80	48	24	15	11	8	6	4.5	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	700W	1000W	1400W
BU1006F	180	90	60	25	18	12	9	5	-	-
BU1006F+M B 1006Fx1	360	240	120	70	40	30	24	15	-	-
BU1006F+M B 1006Fx2	720	360	240	100	70	55	37	25	-	-
BU606F	150	90	40	19	12	5(420W)	-	-	-	-
BU2006 II	---	150	100	70	50	40	28	20	14	5
BU2006 II + M B 2006 II x1	480	300	210	150	100	80	70	50	30	20
BU2006 II + M B 2006 II x2	720	600	360	210	150	120	100	70	60	33
BU1006 II	180	80	50	23	18	10	8	5	-	-
BU1006 II + M B 1006 II x1	300	180	100	55	33	28	23	14	-	-
BU606 II	120	60	30	18	10	5(420W)	-	-	-	-
BU200XR2	420	240	120	80	50	35	28	17	10	5
BU200XR2+MB200XR2x1	780	480	360	180	100	80	65	40	30	17
BU200XR2+MB200XR2x2	1320	900	420	270	180	120	100	70	50	32
BU100XR2	180	120	60	35	20	15	10	5	-	-
BU100XR2+MB100XR2	720	420	240	120	80	60	50	30	-	-
BU100XS	180	120	60	35	20	15	10	5	-	-
BU100XS+MB100XSU	720	420	240	120	80	60	50	30	-	-
BU70XS	120	75	40	20	12	7	5(490W)	-	-	-
BU50XS	120	75	40	20	12	8(350W)	-	-	-	-

型式/負荷容量	20W	50W	100W	200W	300W	400W	600W	800W
BH100PCW (*3)	100	70	45	25	14	10	5	4(700W)
BH100PCW+BHM100PCx1	210	140	95	50	35	25	15	12(700W)
BH100PCW+BHM100PCx2	320	220	140	80	55	40	25	20(700W)
BH100PCW+BHM100PCx3	430	300	190	110	75	55	35	30(700W)
BH100PCW+BHM100PCx4	550	380	260	140	95	70	45	40(700W)
BH60PCW (*3)	65	40	23	13	8	5.1	5(420W)	-

(*3)BH60PCW、BH100PCW 共にバッテリーユニットが標準添付されており、基本構成は2ユニット構成です。

●ラインインタラクティブ方式

時間単位：(分)

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	600W	700W	800W	900W	1000W
BN150XR	220	130	70	37	20	15	11.3	9	6.9	5.5	4.6	4

型式/負荷容量	20W	50W	100W	200W	300W	400W	600W	800W	1000W	1200W	1400W	1600W	1800W	2000W	2300W	2700W
BN300S	900	600	320	150	88	64	38	25	18	15	12	10	8.4	7.5	6	5
BN220S	900	600	320	150	88	64	38	25	18	15	12	10	8.4	7(1980W)	-	-
BN150S	620	290	140	60	35	24	13	9	7	5.5	5(1350W)	-	-	-	-	-
BN100S	620	290	140	60	35	24	13	9	7.9(900W)	-	-	-	-	-	-	-
BN75S	230	109	49	21	12	8.2	4.6	3.5(680W)	-	-	-	-	-	-	-	-
BN50S	230	109	49	21	12	8.2	5.5(450W)	-	-	-	-	-	-	-	-	-

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	700W	1000W
BN140XS	360	180	100	50	32	21	16	10	5(940W)
BN100XS	240	120	60	35	21	15	11	5(670W)	-
BN75XS	150	80	40	20	12	7	5	-	-
BN50XS	150	80	40	20	12	8(335W)	-	-	-

●常時商用給電方式

時間単位：(分)

型式/負荷容量	20W	50W	100W	200W	300W	400W	500W	700W
BU1004X3(*2)	60	60	55	25	20	12	8	5
BU504X4/BU504XL4(*2)	60	60	30	14	8	5	-	-
BU251X(*1)	70	30	10	5(165W)	-	-	-	-
BX75XS2(*1)	90	90	50	22	12	7	5(450W)	-
BX50XFV/BX50XFS(*1)	90	50	20	6	3.5	-	-	-
BX35XFV/BX35XFS(*1)	90	50	20	6	5(210W)	-	-	-
BX25XT(*1)	40	22	8	3.5(168W)	-	-	-	-
BX50LS(*1)	90	50	20	6	3	-	-	-
BZ50LT(*1)	90	45	19	6	3	-	-	-
BZ50T(*1)	90	45	19	6	3	-	-	-
BZ35T(*1)	74	28	10	3	-	-	-	-

(*1)最大バックアップ時間の制限があります。90分以上のバックアップはできません。

(*2)最大バックアップ時間の制限があります。60分以上のバックアップはできません。