

旧機種	後継機種	ハード ○ : 互換あり × : 互換なし		
		出力容量	バッテリー	外形寸法(W×D×Hmm) 旧機種 ↓ 後継機種
常時商用給電方式 (BUシリーズ)				
BU181X	BZ35LT2	○	×	360×76×73 ↓ 300×123.5×86.5
BU250X	BZ35LT2	○	×	420×360×45 ↓ 300×123.5×86.5
BU351X	BZ50LT2	○	×	100×340×190 ↓ 300×123.5×86.5
BU351XL	BX50F	○	×	380×335×45 ↓ 287×287×45
BU504X	BX75SW	○	×	100×340×190 ↓ 90×287×278
BU504XII	BX75SW	○	×	100×340×190 ↓ 90×287×278
BU504XIII	BX75SW	○	×	100×340×190 ↓ 90×287×278
BU504XL	BX75SW	○	×	380×335×45 ↓ 90×287×278
BU504XLII	BX75SW	○	×	380×335×45 ↓ 90×287×278
BU504XLIII	BX75SW	○	×	380×335×45 ↓ 90×287×278
BU1004XL	BU100RW	○	×	420×395×80 ↓ 438×474×87
BU1004XLII	BU100RW	○	×	420×395×80 ↓ 438×474×87
常時商用給電方式 (BXシリーズ)				
BX3	BX35F	○	×	190×335×41×2BOX ↓ 287×287×45
BX350	BX35F	○	×	285×287×45 ↓ 287×287×45
BX351	BX50FW	○	×	285×287×45 ↓ 287×287×45
BX352	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX35LF	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX35XF	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX5	BX50F	○	×	190×335×41×2BOX ↓ 287×287×45
BX500	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX500II	BX50FW	○	×	80×230×170 ↓ 287×287×45
BX50LF	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX50XF	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX510	BY50FW	○	×	285×287×45 ↓ 287×330×45
BX750	BX75SW	○	×	130×305×165 ↓ 90×287×278
BX75XS	BX75SW	○	×	130×305×165 ↓ 90×287×278

ラインインタラクティブ方式 (BNシリーズ)				
BN1250	BN150T	○	×	179 × 439 × 200 ↓ 172 × 415 × 225
常時インバータ給電方式 (BUシリーズ)				
BU501	BU75RW	○	×	420 × 400 × 65 ↓ 438 × 474 × 87
BU501F	BU60RE	○	×	480 × 370 × 99 ↓ 434 × 462 × 85
BU502	BU75RW	○	×	420 × 400 × 65 ↓ 438 × 474 × 87
BU503F	BU60RE	○	×	480 × 402 × 95 ↓ 434 × 462 × 85
BU601	BU75SW	○	×	150 × 400 × 265 ↓ 145 × 395 × 224
BU601L	BU75RW	○	×	420 × 400 × 73 ↓ 438 × 474 × 87
BU602F	BU60RE	○	×	415 × 395 × 95 ↓ 434 × 462 × 85
BU606	BU75SW	○	×	210 × 400 × 73 × 2BOX ↓ 145 × 395 × 224
BU707	BU75SW	○	×	145 × 397 × 224.5 ↓ 145 × 395 × 224
BU70XR	BU75RW	○	×	440 × 445 × 88 ↓ 438 × 474 × 87
BU1001H	BU100RW	○	×	250 × 520 × 570(キャスター付) ↓ 438 × 474 × 87
BU1001HII	BU100RW	○	×	250 × 520 × 567(キャスター付) ↓ 438 × 474 × 87
BU1001L	BU100RW	○	×	250 × 520 × 318(キャスター付) ↓ 438 × 474 × 87
BU1001LII	BU100RW	○	×	250 × 520 × 318(キャスター付) ↓ 438 × 474 × 87
BU1002F	BU100RE	○	×	415 × 395 × 95 × 2BOX ↓ 434 × 462 × 85
BU1003	BU100SW	○	×	170 × 450 × 320 ↓ 145 × 395 × 224
BU1006	BU100RW	○	×	210 × 480 × 95 × 2BOX ↓ 438 × 474 × 87
BU1007	BU100SW	○	×	145 × 397 × 224.5 ↓ 145 × 395 × 224
BU100XR	BU100RW	○	×	440 × 445 × 88 ↓ 438 × 474 × 87
BU100XR(B)	BU100RW	○	×	440 × 445 × 88 ↓ 438 × 474 × 87
BU1501	BU150SW	○	×	320 × 600 × 352 ↓ 145 × 480 × 224
BU2006	BU200RW	○	×	220 × 436 × 128 × 2BOX ↓ 438 × 550 × 130
BU200XR	BU200RW	○	×	440 × 426 × 88 × 2BOX ↓ 438 × 550 × 130
BU200XR(B)	BU200RW	○	×	440 × 426 × 88 × 2BOX ↓ 438 × 550 × 130