

■ Synology NAS - オムロンUPS 対応一覧表 ■

形状	形状	形状	形状	形状	タワー (18シリーズ)					タワー (16シリーズ)				
					シリーズ名									
					DS918+	DS718+	DS418play	DS218+	DS916+	DS716+ II	DS716+	DS416play	DS216+II	DS216+
					Linux	Linux	Linux	Linux	Linux	Linux	Linux	Linux	Linux	Linux
消費電力(負荷時 W)	28.80	20.10	29.01	17.23	30.00	19.20	25.84	29.00	17.40	17.60				
外観														
外観														
形状	形状	形状	形状	形状	形状	形状	形状	形状	形状	形状				
ラック	イン パー タ		[BU-RW] BU300RW BU200RW BU100RW/BU75RW	USB	-	-	-	-	-	-	-	-	-	-
			RS232C	-	-	-	-	-	-	-	-	-	-	
			接点	-	-	-	-	-	-	-	-	-	-	
	ライン		[BN-R] BN300R BN150R BN75R	USB	●	●	●	●	●	●	●	●	●	●
				RS232C	-	-	-	-	-	-	-	-	-	-
				接点	-	-	-	-	-	-	-	-	-	-
			[BN-XR] BN150XR	USB	-	-	-	-	-	-	-	-	-	-
				RS232C	-	-	-	-	-	-	-	-	-	-
				接点	-	-	-	-	-	-	-	-	-	-
タワー	イン パー タ		[BU-SW] BU100SW BU100SW BU75SW/BU50SW	RS232C	-	-	-	-	-	-	-	-	-	-
				接点	-	-	-	-	-	-	-	-	-	-
				LAN	-	-	-	-	-	-	-	-	-	-
	ライン		[BL-T] BL100T BL75T BL50T	USB	-	-	-	-	-	-	-	-	-	-
				RS232C	-	-	-	-	-	-	-	-	-	-
				接点	-	-	-	-	-	-	-	-	-	-
			[BN-T] BN50T ※1	USB	●	●	●	●	●	●	●	●	●	
				RS232C	-	-	-	-	-	-	-	-	-	-
				接点	-	-	-	-	-	-	-	-	-	-
	常 時 商 用		[BW-T] BW120T/BW100T BW55T/BW40T	USB	-	-	-	-	-	-	-	-	-	
				接点	-	-	-	-	-	-	-	-	-	
				LAN	-	-	-	-	-	-	-	-	-	
フ ラ ツ ト		[BY-S] BY120S/BY80S BY50S/BY35S	USB	●	●	●	●	●	●	●	●			
			接点	-	-	-	-	-	-	-	-	-		
			LAN	-	-	-	-	-	-	-	-	-		
テ ー プ ル		[BY-W] BY75SW BY50FW	USB	-	-	-	-	-	-	-	-	-		
			RS232C	-	-	-	-	-	-	-	-	-		
			接点	-	-	-	-	-	-	-	-	-		
フ ラ ツ ト		[BX-W] BX75SW BX50FW	RS232C	-	-	-	-	-	-	-	-	-		
			接点	-	-	-	-	-	-	-	-	-		
			LAN	-	-	-	-	-	-	-	-	-		
フ ラ ツ ト		[BX-F] BX50F BX35F	USB	-	-	-	-	-	-	-	-	-		
			接点	-	-	-	-	-	-	-	-	-		
			LAN	-	-	-	-	-	-	-	-	-		
テ ー プ ル		[BZ-LT2] BZ50LT2 BZ35LT2	USB	-	-	-	-	-	-	-	-	-		
			接点	-	-	-	-	-	-	-	-	-		
			LAN	-	-	-	-	-	-	-	-	-		
推奨UPS				BY50S	BY50S	BY50S	BY50S	BY50S	BY50S	BY50S	BY50S	BY50S		
コメント														

当社UPSをご使用いただく場合は、6.2.1-23824以降のバージョンのDSMにてご使用ください。(これより以前のDSMの場合はアップデートが必要です)
 ※ 1 BN75T/BN100T/BN150T/BN220T/BN300Tについては未検証です。
 ●:標準対応 ○:オプション対応 -:未対応または未検証