

形状		ラック																
シリーズ名		WSS420RNS2	WSS420RNS2	WSS420RNS2	WSS420RNS2	WSS420RNS9	WSS420RNS9	WSS420RNS9	WSS420RNS9	TSS420RN	TS3420RN	TSS1220RH	TSS1210RH	TS11210RH	TS6400RN			
OS		Windows Server IoT 2022 for Storage Standing	Windows Server IoT 2022 for Storage Workgroup	Windows Server IoT 2022 for Storage Standing	Windows Server IoT 2022 for Storage Workgroup	Windows Server IoT 2019 for Storage Standing	Windows Server IoT 2019 for Storage Workgroup	Windows Server IoT 2019 for Storage Standing	Windows Server IoT 2019 for Storage Workgroup	Linux	Linux	Linux	Linux	Linux	Linux			
最大消費電力(W)		100	100	100	100	100	100	100	100	100	100	500	500	500	100			
形状	回転方式	シリーズ名	外形	外形														
				1/F	2/F	3/F	4/F	5/F	6/F	7/F	8/F	9/F	10/F	11/F	12/F			
ラック	インターフェイス	シリーズ名	外形	接続														
				USB	RS232C	LAN	LAN	LAN	LAN	LAN	LAN	LAN	LAN	LAN	LAN	LAN	LAN	
ラック	インターフェイス	[BU-RW] BU300RW BU300RW BU100RW/BU150RW		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
ラック	インターフェイス	[BN-R] BN300R BN150R BN75R		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
タワー	インターフェイス	[BU-SW] BU150SW BU100SW BU150SW/BU50SW		RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
				LAN	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2	○:※2
タワー	インターフェイス	[BL-T] BL100T BL15T BL50T		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
タワー	インターフェイス	[BN-T] BN300T/BN220T BN150T/BN100T BN75T/BN50T		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
フラット	常時商用	[BW-T] BW120T/BU100T BW55T/BU40T		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
フラット	常時商用	[BY-S] BY120S/BY80S BY50S/BY35S		USB	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●:※1	●	●	●	●	●	●
				RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
フラット	常時商用	[BX-W] BX75SW BX50FW		RS232C	—	—	—	—	—	—	—	—	—	—	—	—	—	—
				接続	—	—	—	—	—	—	—	—	—	—	—	—	—	—
フラット	常時商用	[BX-F] BX30F BX35F		USB	—	—	—	—	●:※1	●:※1	●:※1	●:※1	—	—	—	—	—	—
				接続	—	—	—	—	—	—	—	—	—	—	—	—	—	—
テーブル	常時商用	[BZ-LT2] BZ50LT2 BZ35LT2		USB	—	—	—	—	●:※1	●:※1	●:※1	●:※1	—	—	—	—	—	
推奨UPS		BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	BN75R	
コメント		●:標準対応 ○:オプション対応 —:未対応																

※1 NAS側にネットワークアダプタ「PowerAct Pro」もしくは「Simple Shutdown Software」のインストールが必要です。
 ※2 別売のネットワークアダプタが必要です。またNAS側にネットワークアダプタ「PowerAct Pro」のインストールが必要です。
 ※3 一部、対応していない機種(BL50T/BN50T/BW55T/BW40T/BY50S/BY35S)があります。

形状					タワー		
シリーズ名					LS220DNB LS210DNB LS220DB	LS421D LS420D LS410D LS410DX	
OS					Linux	Linux	
最大消費電力(W)					48	48	
形状	運転方式	シリーズ名	外観	I/F	外観		
ラック	インバータ	[BU-RW] BU300RW BU200RW BU100RW/BU75RW		USB	●	●	
				RS232C	-	-	
				接点	-	-	
				LAN	-	-	
	ライン	[BN-R] BN300R BN150R BN75R		USB	●	●	
				RS232C	-	-	
タワー	インバータ	[BU-SW] BU150SW BU100SW BU75SW/BU50SW		RS232C	-	-	
				接点	-	-	
				LAN	-	-	
	ライン	[BN-T] BN300T/BN220T BN150T/BN100T BN75T/BN50T		USB	●	●	
				RS232C	-	-	
				接点	-	-	
				LAN	-	-	
	フラット	常時商用	[BY-S] BY120S/BY80S BY50S/BY35S		USB	●	●
					BY75SW BY50FW		USB
			[BX-W] BX75SW BX50FW		RS232C	-	-
					接点	-	-
			[BX-F] BX50F BX35F		USB	●	●
テーブル	[BZ-LT2] BZ50LT2 BZ35LT2		USB	●	●		
推奨UPS					BY35S	BY35S	
コメント							

●:標準対応 ○:オプション対応 -:未対応